

SPECIFICATION SHEET

MHZ SMD CERAMIC RESONATOR CASE 6030 CP SERIES

| SPECIFICATION SHEET NO. | R1015- CP7M370000S030 | | |
|-------------------------|---|--|--|
| ORIGINAL MFG/PART NO | TGS Crystals/CRTP 7.37MG-30TLH/ZTTCP7.37MG-30 | | |
| DATE | Oct. 15, 20 | 024 | |
| REVISION | A1 | Updated With Most Recent Data | |
| DESCRIPTION AND | MHz SMD | Ceramic Resonator, 3 Pads, CP Series | |
| | Case 6030 |), Dimension L6.0*W3.0*H1.5mm | |
| MAIN PARAMETRICS | 7.37MHz, | Frequency Accuracy \pm 0.5%; Built-in Capacitance 30pF | |
| | Operating | Temp. Range -25°C ~+85°C | |
| | Reflow Pro | ofile Condition 260 °C Max. | |
| | Package ir | n Tape/Reel, 4000pcs/Reel | |
| | REACH/Ro | HS/RoHS III Compliant, RoHS Annex III lead Exemption | |
| | (Exempt per RoHS EU 2015/863) | | |
| CUSTOMER | | | |
| CUSTOMER PART NUMBER | | | |
| CROSS REF. PART NUMBER | | | |
| МЕМО | | | |
| | | | |

| VENDOR APPROVE | | | |
|-------------------------|-----------------------------------|-------------------------------------|-----------------------|
| Issued/Checked/Approved | Comporte Se Mandy Se You Xu | Compose Ruby Zhang Polysou | Jack Jack Trays |
| Date: Oct. 15, 2024 | | | |

CUSTOMER APPROVE Date: 10/15/2024



PART CODE: **CP7M370000S030** MHZ SMD CERAMIC RESONATOR CASE 6030 CP SERIES

MAIN FEATURE

- MHz SMD Ceramic Resonator, 3 pads, Case 6030,
- Case Dimension L6.0*W3.0*H1.5mm
- Low Cost And Short Shipment
- Built-in Capacitance
- Reflow Profile Condition 260 °C Max.
- REACH/RoHS/RoHS III compliant, RoHS Annex III lead Exemption

(Exempt per RoHS EU 2015/863)

APPLICATION

- Communication Electronics and More
- Bluetooth, Wireless Communication Set

HOW TO ORDER

• Please follow up part code guide and indicate part code when you order or RFQ.

PART CODE GUIDE

| CODE | NAME | KEY SPECIFICATION OPTION |
|------|--------------------|---|
| СР | Product Series | MHz SMD Ceramic Resonator, 3 pads, Case 6030 Dimension L6.0*W3.0*H1.5mm |
| 7M37 | Frequency Range | 7M37: 7.37MHz |
| 0000 | Internal Control | Letter or Digits (A~Z, a~z or 1~9) |
| S | SMD Type Package | Tape/Reel |
| 030 | Special Parametric | Letter or Digits (A~Z, a~z or 1~9) |
| - XX | Suffix | Blank: N/A XX: Internal Control Code, Letter A~Z, a~z or digits (0~9) for Special/Custom Parameters |

10/15/2024

NextGen Components, Inc.



Image shown is a representation only. Exact specifications should be obtained from the product dimension.








MHZ SMD CERAMIC RESONATOR CASE 6030 CP SERIES


DIMENSION (Unit: mm)

Case 6030, 3 Pads

L6.0*W3.0*H1.5mm

Top View






Connection


1 Input

2 Ground

③ Output

Side View






10/15/2024



MEASUREMENT

- Parts shall be tested under the condition (Temp.: 20±15°C, Humidity 65±20% R.H.) unless the standard condition (Temp.: 25±3 °C, Humidity : 65±10% R.H.) is regulated to measure.
- Measuring Circuit



GENERAL ELECTRICAL SPECIFICATIONS AND RATING

| PARAMETER | SYMBOLS | VALUE | UNITS | CONDITION |
|---|---------|------------|----------|---|
| Withstanding Voltage | - | 100 | V | @DC, 5s Max. |
| Insulation Resistance | Ri | 500 Min. | mΩ | @10V, 1min. |
| Operating Temperature Range | ΓJ | -25 to +85 | °C | |
| Storage Temperature Range | Т sтg | -55 to +85 | °C | |
| Rating Voltage | U r | 6 | V DC | |
| | | 15 | V p-p AC | |
| Temperature Coefficient of Oscillation Frequency | | ±0.3 Max. | % | Oscillation Frequency drift, -25℃ ~ +85℃ |
| Oscillation Frequency Aging Rate * | | ±0.1 Max. | | From initial value |

Note: * : Components shall be left in a chamber of +85 \pm 2 °C for 1000 hours, then measured after leaving in natural condition for 1 hours. View

10/15/2024



MHZ SMD CERAMIC RESONATOR CASE 6030 CP SERIES

ELECTRICAL CHARACTERISTICS - FOR DIFFERENT PART CODE

| PART CODE | Center Frequency (F0) | Frequency Accuracy | Resonant Impedance Ro | Built-in Capacitance C1, C2 |
|----------------|--------------------------|--------------------|--------------------------|--------------------------------|
| | MHz | % | Ω | pF |
| CP2M000000S015 | 2.00 | ±0.5 | 100 | 15 (1±20%) |
| CP2M0000005030 | 2.00 | ±0.5 | 100 | 30 (1±20%) |
| CP2M0000005047 | 2.00 | ±0.5 | 100 | 47 (1±20%) |
| CP2M450000S030 | 2.45 | ±0.5 | 100 | 30 (1±20%) |
| CP2M500000S030 | 2.50 | ±0.5 | 100 | 30 (1±20%) |
| CP2M500000S047 | 2.50 | ±0.5 | 100 | 47 (1±20%) |
| CP3M000000S030 | 3.00 | ±0.5 | 40 | 30 (1±20%) |
| CP3M580000S015 | 3.58 | ±0.5 | 40 | 15 (1±20%) |
| CP3M580000S030 | 3.58 | ±0.5 | 40 | 30 (1±20%) |
| CP3M580000S033 | 3.58 | ±0.5 | 40 | 33 (1±20%) |
| CP3M580000S047 | 3.58 | ±0.5 | 40 | 47 (1±20%) |
| CP3M680000S030 | 3.68 | ±0.5 | 30 | 30 (1±20%) |
| CP3M680000S033 | 3.68 | ±0.5 | 30 | 33 (1±20%) |
| CP4M0000005010 | 4.00 | ±0.5 | 40 | 10 (1±20%) |
| CP4M000000S015 | 4.00 | ±0.5 | 40 | 15 (1±20%) |
| CP4M000000S030 | 4.00 | ±0.5 | 40 | 30 (1±20%) |
| CP4M0000005033 | 4.00 | ±0.5 | 40 | 33 (1±20%) |
| CP4M190000S030 | 4.19 | ±0.5 | 30 | 30 (1±20%) |
| CP4M910000S015 | 4.91 | ±0.5 | 25 | 15 (1±20%) |
| CP4M910000S030 | 4.91 | ±0.5 | 30 | 30 (1±20%) |

10/15/2024



MHZ SMD CERAMIC RESONATOR CASE 6030 CP SERIES

ELECTRICAL CHARACTERISTICS - FOR DIFFERENT PART CODE

| PART CODE | Center Frequency (F0) | Frequency Accuracy | Resonant Impedance Ro | Built-in Capacitance C1, C2 |
|----------------|--------------------------|--------------------|--------------------------|--------------------------------|
| | MHz | % | Ω | pF |
| CP5M000000S030 | 5.00 | ±0.5 | 40 | 30 (1±20%) |
| CP6M000000S030 | 6.00 | ±0.5 | 30 | 30 (1±20%) |
| CP7M370000S030 | 7.37 | ±0.5 | 30 | 30 (1±20%) |
| CP8M000000S015 | 8.00 | ±0.5 | 30 | 15 (1±20%) |
| CP8M000000S030 | 8.00 | ±0.5 | 30 | 30 (1±20%) |
| CP8M000000S033 | 8.00 | ±0.5 | 30 | 33 (1±20%) |
| CP8M000000S047 | 8.00 | ±0.5 | 30 | 47 (1±20%) |
| CP10M00000S030 | 10.0 | ±0.5 | 30 | 30 (1±20%) |
| CP12M00000S030 | 12.0 | ±0.5 | 30 | 30 (1±20%) |
| CP20M00000S010 | 20.0 | ±0.5 | 60 | 10 (1±20%) |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |

10/15/2024



MHZ SMD CERAMIC RESONATOR CASE 6030 CP SERIES

PHYSICAL AND ENVIRONMENTAL CHARACTERISTICS

| TEST ITEMS | TEST METHOD AND CONDITIONS | REQUIREMENT |
|------------------------|---|--|
| Humidity | Keep the resonator at $60^{\circ}C \pm 2^{\circ}C$ and 90% -95% RH for 240h. Then Release the resonator into the room Condition for 1h prior to the Measurement. | It shall fulfill Table 1 |
| High Temperature | Subject the resonator to $85^{\circ}C \pm 2^{\circ}C$ for 240h, then release the resonator into the room conditions for 1h prior to the measurement. | It shall fulfill Table 1 |
| Low Temperature | Subject the resonator to -40°C \pm 2°C for 240h, then release the resonator into the room conditions for 1h prior to the measurement. | It shall fulfill Table 1 |
| Temperature Cycling | After temperature cycling of blow table was performed 5 times, discriminator shall be measured after being placed in natural conditions for 1h. Temp.: −25±3°C, Time: 30±3 min ; Temp.: 85±3°C, Time: 30±3 min. | lt shall fulfill Table 1 |
| Vibration | Subject the resonator to vibration for 2h each in x_x y and z axis With the amplitude of 1.5mm, the frequency shall be varied uniformly between the limits of 10 Hz—55Hz. | It shall fulfill Table 1 |
| Mechanical Shock | Drop the resonator randomly onto a wooden floor from the height of 100cm 3 times. | No visible damage and it shall fulfill Table 1. |
| Soldering Test | Components shall be measured after applying twice of the re-flow soldering with following temperature profile and leaving in natural condition for 1 hour. | It shall fulfill Table 1 |
| Solderability | Dipped in 245°C \pm 5°C solder bath for 3s \pm 0.5 s with rosin flux (25wt% ethanol solution.). see <i>Suggested Reflow Profile</i> | The terminals shall be at least 95% covered by solder. |
| Board Bending | Mount on a glass-epoxy board(width =40mm, thickness=1.6mm),then bend it to 1mm displacement(velocity= 1mm/s) and keep it for 5s. | Mechanical damage such as break shall not occur |




MHZ SMD CERAMIC RESONATOR CASE 6030 CP SERIES


Table 1

| TEST ITEMS | CHARACTERISTICS AFTER TEST | | | |
|---|----------------------------|-------|--|--|
| | VALUE | UNITS | | |
| Oscillation Frequency Change △Fosc/Fosc | ±0.3 Max | % | | |
| Resonant Impedance $	riangle$ Ro | 30 Max. | Ω | | |
| Note: The limits in the above table are referenced to the initial measurements. | | | | |

Soldering Test



Board Bending




10/15/2024




MHZ SMD CERAMIC RESONATOR CASE 6030 CP SERIES

SUGGESTED REFLOW PROFILE (For Reference Only)



RECOMMENDED LAND PATTERN




10/15/2024




PART CODE: **CP7M370000S030** MHZ SMD CERAMIC RESONATOR CASE 6030 CP SERIES

TPAE/REEL DIMENSIONS (Unit: mm)




| CODE | DIMENSION |
|-------------------|-----------|
| фА | 330±3.0 |
| фВ | 80 Min. |
| W | 16.4 Min. |
| т | 22.4 Max. |
| Qty. Per Reel | 4000pcs |
| Carrier Tape Size | 16 |

PACKING METHOD SKETCH MAP



TEST CONDITION OF PEELING STRENGTH



10/15/2024



CAUTION

- Don't apply excess mechanical stress to the component and terminals at soldering. Do not use this product with bend.
- Do not clean or wash the component for it is not hermetically sealed.
- Do not use strong acidity flux, more than 0.2wt% chlorine content, in flow soldering.
- Don't be close to fire.
- This specification mentions the quality of the component as a single unit. Please insure the component is thoroughly evaluated in your application circuit
- Expire date (Shelf life) of the products is 12 months after delivery under the conditions of a sealed and an unopened package. Please use the products within 12 months after delivery. If you store the products for a long time (more than 12 months), use carefully because the products may be degraded in the solder-ability or rusty. Please confirm solder-ability and characteristics for the products regularly.
- Exposure components under soldering condition that is exceeding our recommendation will increase the failure dangerous.
- Please contact us before using the product as automobile electronic component.
- Please return one of these specifications after your signature of acceptance.
- When something gets doubtful with this specifications, we shall jointly work to get an agreement.
- For questions on technology, prices and delivery, please contact our sales offices or e-mail:

sales@NextGenComponent.com .

11



IMPORTANT NOTES AND DISCLAIMER

- ROHS COMPLIANCE: The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU RoHS Directive (EU) 2015/863 EC (RoHS3). RoHS Test Report for this product can be obtained at Download Center.
- REACH COMPLIANCE: REACH substances of high concern (SVHCs) information is available for this product.
 Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, REACH Test Report for this product can be obtained at Download Center.
- All Product parametric performance is indicated in the Electrical Characteristics for the listed herein test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.
- 4. NextGen Component, Inc (*NextGen*) reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.
- 5. NextGen makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, not does NextGen assume any liability for application assistance or customer product design.
- 6. NextGen does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application. No license is granted by implication or otherwise under any intellectual property rights of NextGen.
- 7. NextGen products are not authorized for use as critical components in life support devices or systems without express written approval by NextGen.
- 8. NextGen requires that customers first obtain an RMA (Returned Merchandise Authorization) number prior to returning any products. Returns must be made within 30 days of the date of invoice, be in the original packaging, unused and like-new condition. At the time of quoting or purchasing, a product may say that it is Non-Cancelable/ Non-Returnable (NCNR). These products are not returnable and not refundable.