

SPECIFICATION FOR ELECTRO-MAGNET TRANSDUCER

TOTAL PAGE 07 <u>www.be-star.com</u> RoHS

Customer		Model Name	BMT1212H09 LF		
Customer P/N		Product No.	010243		
Date	15 Mar.11	Issue No.	BS/TET01.971C		
Page	01 of 06	Issue Date	11/03/15		

Approval:

- 1.Characteristics
- 2.Dimension
- 3.Reliability Test
- 4.Packing
- 5.Notice
- 6. History change record

Drawn by	Checked by	Approved by	Customer approved
魏奉珍	陶红仲	张秀琴	

BESTAR ELECTRONICS INDUSTRY CO.,LTD

No.199 HuangHe West Road.New district, ChangZhou, JiangSu Province, P.R. China



BMT1212H09 LF


1. Characteristics

1.1Electrical and Mechanical Characteristics

No.	Item	Specifications					
1	Operating Voltage	716Vo-p					
2	Rated Voltage	12Vo-p					
3	Coil Resistance	140± 12 Ω					
4	** Coil Impedance	240 Ω					
5	* Sound Output at 10cm	≥ 85dB					
6	Resonant Frequency	2400Hz					
7	* Rated Current	≤40mA					
8	Operating Temperature	-40+85°C					
9	Storage Temperature	-40+85°C					
10	Weight	2g					
* Value applying rated voltage (2400Hz, 1/2duty,square wave)							
	**Value applying(2400Hz square wave measuring current 60 µ A)						

Value applying(2400Hz,square wave,measuring current 60 μ A)


1.2 Test method:



	С	11/03/15					BMT1212H09 LF			
Ī	В	08/03/12	魏奉玲	ROHS	Drawn by:	魏奉玲	DIVIT 1212HU9 LF			
Α	Α	02/07/01	王善梅		Checked by:	陶红仲	Transducer			A
	Rev.	Rev. Date Drawn Note Approved by: 张秀琴					Transducei			
	BESTAR ELECTRONICS INDUSTRY CO.,LTD www.be-star.com wu@be-star.com					DRG NO: BS/TET01.9	71C	Page:2 of 6		
	6 5 4 3						2		1	•

This print and information there in are proprietary to Bestar Electronics Industry Co., Ltd. and shall not be used in whole or in part without its written content








4. Packing

4.1 Packing drawing (unit:mm)

1)100pcs/tray

- 2)50trays/carton
- 3)5000 pcs/carton in total
- 4)carton size 52x42x28cm



5.Notice

- 5.1 The products mustn't be washed
- 5.2 Storage Condition

The products should be stored in the room ,where the temperature/humidity is stable. And avoid suchplaces where there are large temperature changes. Please store the products at the following conditions:

Temperature: -10 to + 40°C Humidity: 15 to 85% R.H.

5.3 Expire Date on Storage

Expire date (Shelf life) of the products is six months after deliveried under the conditions of a sealed and an unopened package. Please use the products within six months after deliveried.

If you store the products for a long time (more than six months), use carefully because the products may be degraded in the solderability and/or rusty. Please confirm solderability and characteristics for the products regularly.

- 5.4 Notice on Product Storage
- (1) Please do not store the products in a chemical atmosphere (Acids, Alkali, Bases, Organic gas, Sulfides and so on), because the characteristics may be reduced at quality, and/or be degraded in the solderability due to the storage in a chemical atmosphere.
- (2) Please use the products immediately after the package is opened, because the characteristics may be reduced at quality, and/or be degraded in the solderability due to storage under the poor condition.

-	1								Н	
	С	11/03/15	魏奉玲	change ca si ze&quan		11/03/15	DMT4040U	BMT1212H09 LF		
	В	08/03/12	魏奉玲	ROHS	Drawn by:	魏奉玲	BIVITIZIZE			
A	Α	02/07/01	7/01 王善梅 Checked by: 陶红仲 Transducer					۵r		
	Rev. Date Drawn Note Approved by: 张秀琴					Transduce	<i>,</i>			
	BESTAR ELECTRONICS INDUSTRY CO.,LTD www.be-star.com wu@be-star.com						DRG NO: BS/TET01.971	1C	Page:5 of 6	
6 5 1 2							2		1	•

This print and information there in are proprietary to Bestar Electronics Industry Co., Ltd. and shall not be used in whole or in part without its written content

C

В



BMT1212H09 LF 6. History change record Change Items version Date Drawn Approved Before No. After Α 02/07/01 王善梅 张秀琴 **ROHS** В 魏奉玲 张秀琴 carton size:50x27x26cm carton size:52x42x28cm С quantity in a carton:3000 pcsquantity in a carton:5000 pcs 魏奉玲 11/03/15 张秀琴 This print and information there in are proprietary to Bestar Electronics Industry Co., Ltd. and shall not be used in whole or in part without its written content change carton size&quantity 11/03/15 魏奉玲 11/03/15 С Date: BMT1212H09 LF 08/03/12 В 魏奉玲 ROHS Drawn by: 魏奉玲 02/07/01 王善梅 Checked by: Α 陶红仲 Transducer 张秀琴 Approved by: Drawn Note BESTAR ELECTRONICS INDUSTRY CO.,LTD DRG NO: BS/TET01.971C Page:6 of 6 www.be-star.com wu@be-star.com