

### Nextreme™ Value Chiller

The Nextreme™ Value Chiller offers OEMs a cost-effective and reliable thermal management solution that keeps sensitive electronics in industrial and analytical equipment at the optimum temperature. Based on the Nextreme Performance Chiller Series design, the Value line offers the same ease of use, low maintenance features and high coefficient of performance (COP) as the performance chiller but at a lower cost to provide a more competitive pricing of an OEM bundled solution. Most importantly, the Value Chiller can be configured to meet unique application requirements. By using environmentally friendly R513A refrigerant, Nextreme Chillers achieve similar performance with half the Global Warming Potential (GWP) compared to traditional hydrofluorocarbon (HFC) refrigerants. Units run on universal input 230V, 50/60Hz, which means that they can operate anywhere in the world.


#### **Features**


- Economical Cooling Solution
- Reliable Performance
- Environmentally Friendly
- User-Friendly
- Application Specific Configurations

### **Applications**

- Mass Spectrometry
- Electron Microscopes Medical Imaging
- Biotech
- Liquid Chromatography
- Medical Lasers
- Industrial Lasers
- Semiconductor Metrology
- Semiconductor Fabrication







## **COOLING POWER OPERATING POINTS**

100% Water / 60Hz / 20°C Ambient Air

Cooling Power (Qc) = 1,250 Watts Fluid Setpoint = 20 °C Fluid  $\Delta T$  @ 10.5 L/min = 1.7 °C

100% Water / 50Hz / 20°C Ambient Air

Cooling Power (Qc) = 1,200 Watts Fluid Setpoint = 20 °C Fluid  $\Delta T$  @ 9.0 L/min = 1.9 °C

100% Water / 60Hz / 30°C Ambient Air


Cooling Power (Qc) = 1,000 Watts Fluid Setpoint = 20 °C Fluid  $\Delta T$  @ 10.5 L/min = 1.4 °C

100% Water / 50Hz / 30°C Ambient Air


Cooling Power (Qc) = 950 Watts Fluid Setpoint = 20 °C Fluid  $\Delta T$  @ 9.0 L/min = 1.5 °C








VRC1200-A1-20-BV1 Cooling Capacity - 50Hz 100% Water Flow = 10.5 L/min




 $\begin{array}{c} \text{VRC1200-A1-20-BV1 Cooling Capacity - 60Hz} \\ \text{60/40 Water-Glycol Flow} = 10.5 \text{ L/min} \end{array}$ 















## VRC1200-A1-20-BV1 - Pump Curve





# **TECHNICAL SPECIFICATIONS**

# **Performance**

Nominal Cooling Capacity <sup>1</sup>	1,250 W
Setpoint Range	5°C to 40°C
Temperature Stability	±0.5°C
Nominal Operating Flowrate (60 Hz)	10.5 L/min @ 5.0 Bar
Nominal Operating Flowrate (50 Hz)	9.0 L/min @ 5.0 Bar
Refrigerant	R 513A
Refrigerant Charge	335 g

# **Operation**

Coolant	Water or Water/Glycol
Operating Temperature <sup>2</sup>	15°C to 40°C
Storage temperature range (w/o coolant)	-25°C to 70°C
Humidity range	30% to 80%
Storage Humidity range	5% to 95%, non-condensing
Altitude	< 2,000 meters
Input Voltage	230 VAC
Frequency	50/60 Hz
Current	< 5.1 Amps
Maximum Forward Pressure	6.5 Bar
Compliance	ANSI / UL / CSA / IEC EN 61010-1 Edition 3


# **Physical**

Height	699 mm
Length	563 mm
Width	482 mm
Weight	58 kg
Coolant Capacity	5 Liters
Couplings	1/2 in NPT



### **STANDARD FEATURES**

Color Touch Screen Display	Simple user interface and detailed communication of system status without the need for alarm codes or symbols.
Semi-Closed Fluid System	Sealed fluid system with breathable reservoir cap (similar to an automobile). This prevents evaporative loses, introduction of bacteria, and the need for components to prevent fluid from draining back into the system when installed below the application.
Optical Fluid Level Switch	Fluid level sensing with no moving parts.
RS-232 Communications	Complete control integration of chiller into higher level assembly control system.



## **NOTES**

- 1. Nominal capacity rating is given at a 20°C setpoint, 20°C ambient temperature, sea level, and 60Hz operation
- 2. For ambient conditions outside this range, please contact Laird Thermal Systems.

Any information furnished by Laird and its agents, whether in specifications, data sheets, product catalogues or otherwise, is believed to be (but is not warranted as being) accurate and reliable, is provided for information only and does not form part of any contract with Laird. All specifications are subject to change without notice. Laird assumes no responsibility and disclaims all liability for losses or damages resulting from use of or reliance on this information. All Laird products are sold subject to the Laird Terms and Conditions of sale (including Laird's limited warranty) in effect from time to time, a copy of which will be furnished upon request.

© Copyright 2023 Laird Thermal Systems, Inc. All rights reserved. Laird™, the Laird Ring Logo, and Laird Thermal Systems™ are trademarks or registered trademarks of Laird Limited or its subsidiaries.

 $Nextreme^{\tiny{\texttt{M}}} \ is \ a \ trademark \ of \ Laird \ Thermal \ Systems, \ Inc. \ All \ other \ marks \ are \ owned \ by \ their \ respective \ owners.$ 

Revision: 01 Date: 08-24-2023 Print Date: 08-24-2023