


ASSEMBLY INSTRUCTIONS:

- 1. FOLD UP ORGANIZER TRAY
- 2. FOLD UP THE INSERT & PLACE IN TRAY
- 3. FOLD UP THE TALL SLEEVE AND WIPES LID AND PLACE IT INTO THE ORGANIZER INSERT AS SHOWN

ASSEMBLY

Description

- Increases productivity by organizing and standardizing bottle and tool placement at the workstation
- Aesthetically improves the appearance of the work area
- Includes openings for bottles, wipes and hand tools
- Includes ESD protective swab holder insert and cover for wipes
- OD Dimension: 16-7/8" x 8-1/8" x 2-3/8"
- Easy assembly, no need for tape, glue, or staples
- Marked with ESD Protective symbol per ANSI/ESD S541
- Custom configurations available
- Static Dissipative Surface Resistance 1×10^6 to $< 1 \times 10^9$ ohms per ANSI/ESD STM11.11
- Impregnated Corrugated material superior material with greater durability than painted material
- Made from 100% Recycled material and is 100% recyclable.
- Made in the United States of America



47553 Universal Organizer, Corrugated

A smaller organizer is available. Click <u>HERE</u> for item 47555.

"It should be understood that any object, item, material or person could be a source of static electricity in the work environment. Removal of unnecessary nonconductors, replacing nonconductive materials with dissipative or conductive materials and grounding all conductors are the principle methods of controlling static electricity in the workplace, regardless of the activity." [ESD Handbook ESD TR20.20 section 2.4 Sources of Static Electricity]



Specifications and procedures subject to change without notice.

Universal Organizer, Corrugated

PROTEKTIVE PAK 13250 MONTE VISTA AVENUE, CHINO, CA 91710 PHONE (909) 627-2578 ProtektivePak.com	DRAWING NUMBER 47553	DATE: December 2024
--	----------------------------	---------------------------