



## Zero Biased Detector With 50 Ohm SMA Male to SMA Female Video Out Operating From 10 MHz to 2 GHz

### TECHNICAL DATA SHEET

PE8010

Zero Biased Detector With 50 Ohm SMA Male to SMA Female Video Out Operating From 10 MHz to 2 GHz

Configuration

Bias Type Zero Biased Detector

Detector PolarityNegativeBody StyleStraightRF Input ConnectorSMA MaleRF Input Impedance50 OhmsVideo Output ConnectorSMA Female

**Electrical Specifications** 

Frequency Range, GHz

Voltage Sensitivity, mV/mW

Tangential Signal Sensitivity

Maximum VSWR

Flatness, dB

± 0.2

Maximum Input Power, dBm

Video Capacitance, pF

0.01 to 2

500

1.2:1

± 0.2

470

**Mechanical Specifications** 

**Temperature** 

Operating Range,deg C 0 to +90

Size

Length, in [mm] 1.21 [30.73] Width/Dia., in [mm] 0.31 [7.87]

RF Input

Type SMA Male

**Video Output** 

Type SMA Female

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant Yes
REACH Compliant 06/18/2012

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Zero Biased Detector With 50 Ohm SMA Male to SMA Female Video Out Operating From 10 MHz to 2 GHz PE8010

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623

Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





# Zero Biased Detector With 50 Ohm SMA Male to SMA Female Video Out Operating From 10 MHz to 2 GHz

### TECHNICAL DATA SHEET

PE8010

#### **Plotted and Other Data**

Notes:

Values at 25 °C, sea level

Zero Biased Detector With 50 Ohm SMA Male to SMA Female Video Out Operating From 10 MHz to 2 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Zero Biased Detector With 50 Ohm SMA Male to SMA Female Video Out Operating From 10 MHz to 2 GHz PE8010

URL: http://www.pasternack.com/50-ohm-sma-zero-biased-detector-negative-10-mhz-2000-mhz-pe8010-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623

Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

### PE8010 CAD Drawing

Zero Biased Detector With 50 Ohm SMA Male to SMA Female Video Out Operating From 10 MHz to 2 GHz

